

AF25 Light CLASSIC

One row bar 25x25

Grid (A) 25, hole diameter 12,5mm

Nr.	B	g
24340	50	34
25013	100	69
25374	150	103
24336	200	138
22946	250	172
24337	300	206
25012	350	241
23283	400	275
25890	450	310
22947	500	344
25894	550	378
21333	600	413
24338	650	447
24339	700	482
21709	750	516
24189	800	550
27470	850	585
25895	900	619
27473	950	654
22948	1000	688
27605	1050	722
24190	1100	757
33282	1150	791
24191	1200	826
21749	1250	860
24188	1300	895
33283	1350	929
24187	1400	963
31855	1450	998
21189	1500	1.032
33284	1600	1.101
33285	1700	1.170
24395	1800	1.238
33286	1900	1.307
23334	2000	1.376

AF40 Light CLASSIC

One row bar 40x40

Grid (A) 40, hole diameter 20mm

Nr.	B	g
25039	120	221
25377	160	294
26505	200	368
25378	240	441
27342	280	514
25379	320	588
27183	360	661
23549	400	735
24945	440	809
25945	480	882
25951	520	956
26611	560	1.029
27444	600	1.103
33296	640	1.176
26612	680	1.250
28465	720	1.323
32702	760	1.397
23550	800	1.470
26610	840	1.544
26613	880	1.617
26685	920	1.691
27445	960	1.764
24495	1000	1.838
26686	1080	1.985
27559	1160	2.132
23551	1200	2.206
24453	1400	2.570
23552	1600	2.941
25033	1800	3.308
31855	1450	3.381
23553	2000	3.676
23554	2400	4.411
23555	2800	5.146
23556	3200	5.882
23557	3600	6.617
23558	4000	7.352
28035	4400	8.087
28036	4800	8.822

AF50 Light CLASSIC

One row bar 50x50

Grid (A) 50, hole diameter 25mm

Nr.	B	g
28149	50	165
28150	100	330
28151	150	495
28152	200	660
28153	250	825
28154	300	990
28156	350	1.155
28155	400	1.320
28157	450	1.485
26933	500	1.650
28615	600	1.990
28495	700	2.310
33297	800	2.240
32654	900	2.985
26935	1000	3.328
28939	1100	3.630
33298	1200	3.960
27693	1300	4.290
33299	1400	4.648
26937	1500	4.950
28618	1600	5.335
33300	1700	5.638
30012	1800	5.940
33301	1900	6.313
26939	2000	6.600
26941	2500	8.100
26943	3000	9.800
26945	3500	11.400
26947	4000	13.000
26949	4500	14.700
26951	5000	16.300
26953	5500	17.900
26955	6000	19.500



ALUFIX CLASSIC bars can be anodized in different colours. The colour natural is standard, black (-1) is available as an alternative. Other colours on request

Other dimensions on request