

**AF25 Light CLASSIC**

Rectangular bar 25x50

Grid (A) 25, hole diameter 12,5mm

Nr.	B	g
55090	50	68
55091	100	136
55092	150	204
55093	200	272
55094	250	340
55095	300	408
55096	350	476
55097	400	544
55098	450	612
55099	500	680
55100	550	748
55101	600	816
55102	650	884
55103	700	952
55104	750	1.020
55105	800	1.088
55106	850	1.156
55107	900	1.224
55108	950	1.292
55109	1000	1.360
55110	1050	1.428
55111	1100	1.496
55112	1150	1.564
55113	1200	1.632
55114	1250	1.700
55115	1300	1.768
55116	1350	1.836
55117	1400	1.904
55118	1450	1.972
55119	1500	2.040
55120	1550	2.108
55121	1600	2.176
55122	1650	2.244
55123	1700	2.312
55124	1750	2.380
55125	1800	2.448
55126	1850	2.516
55127	1900	2.584
55129	2000	2.720

**AF40 Light CLASSIC**

Rectangular bar 40x80

Grid (A) 40, hole diameter 20mm

Nr.	B	g
57400	80	286
57401	120	428
57402	160	571
57403	200	714
57404	240	857
57405	280	1.000
57406	320	1.142
57407	360	1.285
57408	400	1.428
57409	440	1.571
57410	480	1.714
57411	520	1.856
57412	560	1.999
57413	600	2.142
57414	640	2.285
57415	680	2.428
57416	720	2.570
57417	760	2.713
57418	800	2.856
57419	840	2.999
57420	880	3.142
57421	920	3.284
57422	960	3.427
57423	1000	3.570
57424	1040	3.713
57425	1080	3.856
57426	1120	3.998
57427	1160	4.141
57428	1200	4.284
57429	1240	4.427
57430	1280	4.570
57431	1320	4.712
57432	1360	4.855
57433	1400	4.998
57434	1440	5.141
57435	1480	5.284
57436	1520	5.426
57437	1560	5.569
57438	1600	5.712

**AF40 Light CLASSIC**

Rectangular bar 40x80

Grid (A) 40, hole diameter 20mm

Nr.	B	g
57439	1640	5.855
57440	1680	5.998
57441	1720	6.140
57442	1760	6.283
57443	1800	6.426
57444	1840	6.569
57445	1880	6.712
57446	1920	6.854
57447	1960	6.997
57448	2000	7.140
57449	2040	7.283
57450	2080	7.426
57451	2120	7.568
57452	2160	7.711
57453	2200	7.854
57454	2240	7.997
57455	2280	8.140
57456	2320	8.282
57457	2360	8.425
57458	2400	8.568
57459	2440	8.711
57460	2480	8.854
57461	2520	8.996
57462	2560	9.139
57463	2600	9.282
57464	2640	9.425
57465	2680	9.568
57466	2720	9.710
57467	2760	9.853
57468	2800	9.996
57469	2840	10.139
57470	2880	10.282
7471	2920	10.424
57472	2960	10.567
57473	3000	10.710



**i** **ALUFIX CLASSIC** bars can be anodized in different colours. The colour natural is standard, black (-1) is available as an alternative. Other colours on request

**i** Other dimensions on request

